

[See all 64 Products in Family](#)

## TECHSPEC® 200 x 200mm Linear Polarizing Film (XP42-40)



Stock #29-496 **8 In Stock**

⊖ 1 ⊕ €117<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€117,00 each
Qty 11-25	€103,70 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Linear Polarizer

Type:

Note:  
Polarization axis is parallel to marking on protective film.

#### Physical & Mechanical Properties

200.0 x 200.0 ±1.0

Dimensions (mm):

Thickness (mm):  
0.40 ±0.05

Construction:  
Polarizing Film

## Optical Properties

Coating:  
Uncoated, Protective Film on Both Sides

Extinction Ratio:  
9000:1 (nominal at 555nm)

Substrate:   
[Polymer Film XP42-40](#)

Transmission (%):  
Single: 42 ±2  
Parallel: 36.4  
Crossed: <0.004 (nominal at 555nm)

Wavelength Range (nm):  
400 - 700

Polarization Efficiency (%):  
>99.98 (nominal at 555nm)

Transmission, Single (%):  
42 ±2

Transmission, Parallel (%):  
36.4

Transmission, Crossed (%):  
<0.004 (nominal at 555nm)

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 235:  
[Compliant](#)

## Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information



XP44 - Linear Polarizer

