

TECHSPEC® 1" Dia, 2" FL Protected Alum., Spherical Mirror



Stock **#43-339** 3-4 DAYS

- 1 + **€110,00**

ADD TO CART

Qty 1-9
€110,00
Qty 10+
€93,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 2.00
Effective Focal Length EFL (mm): 50.80
Radius of Curvature (mm): 101.60
Aperture (f/#): f/2
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.25
Edge Thickness ET (mm): 6.35
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant