

TECHSPEC[®] 1" Dia, 4" FL UV Enhanced Alum., Spherical Mirror



Stock **#43-541** 20+ In Stock

-

1

+

€135^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	€135,00 each
Qty 10-25	€114,00 each
Qty 26-49	€107,00 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

25.40 +0/-0.3

Diameter (mm):

Ground

Back Surface:

1.0	Diameter (inches):
+0/-0.01	Diameter Tolerance (inches):
0.25	Edge Thickness ET (inches):
6.35	Edge Thickness ET (mm):
+0.0/-15	Edge Thickness Tolerance (%):

Optical Properties

Metal	Coating Type:
Enhanced Aluminum (250-700nm)	Coating:
250 - 700	Wavelength Range (nm):
101.60	Effective Focal Length EFL (mm):
BOROFLOAT®	Substrate: ☐
f/4	Aperture (f/#):
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
4.00	Effective Focal Length EFL (inches):
±2	Focal Length Tolerance (%):
λ/4	Surface Accuracy:
60-40	Surface Quality:
0.5 J/cm ² @ 355nm, 10ns	Damage Threshold, Reference: ☐
203.20	Radius of Curvature (mm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- [λ/8 Precision Spherical Mirrors](#) Also Available

TECHSPEC® λ/4 Precision Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors are available in a wide range of metallic coating options covering the UV, VIS, and IR spectrum. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® λ/4 Precision Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

Technical Information



;