

[See all 15 Products in Family](#)

1X Mitutoyo Plan Apo Infinity Corrected Long WD Objective

See More by [Mitutoyo](#)



1X Mitutoyo Plan Apo Infinity Corrected Long WD Objective, #58-235

Stock **#58-235** 1 In Stock

-

1

+

€3.185^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€3.185,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
378-800-12	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:

Manufacturer:		Mitutoyo
Physical & Mechanical Properties		
Length excluding Threads (mm):		84.00
Maximum Diameter (mm):		31.5
Weight (g):		300.00
Exit Pupil Diameter (mm):		10.00
Optical Properties		
Compatible Cover Glass Thickness (mm):		N/A
Horizontal Field of View, 1/2" Sensor:		6.40mm
Horizontal Field of View, 2/3" Sensor:		8.80mm
Focal Length FL (mm):		200.00
Magnification:		1X
Numerical Aperture NA:		0.025
Resolving Power (µm):		11.0
Depth of Field (µm):		440.00
Field of View, 24 Diameter Field Eyepiece (mm):		24.00
Field of View, 18 Diameter Field Eyepiece (mm):		18.00
Working Distance (mm):		11.0
Wavelength Range (nm):		435 - 655
Parfocal Length (mm):		95
Immersion Liquid:		N/A
Sensor		
Maximum Sensor Format:		2/3"
Threading & Mounting		
Mounting Threads:		M26 x 36 TPI
Environmental & Durability Factors		
Operating Temperature (°C):		+5 to +40
Operating Humidity:		20 - 80%
Regulatory Compliance		
RoHS 2015:		Exempt
Certificate of Conformance:		View
REACH 241:		Contains SVHC(s)

Product Details

Note: If this objective is being used with the VMJ-HR (EO 23338), use the included ¼ wavelength plate in conjunction with the Polarizer-Analyzer (EO 71009). This will help reduce flares or stray light.

- Long Working Distances
- Bright Field Inspection
- High Quality Plan Apochromat Design
- Flat Image Surface over Entire Field of View

Mitutoyo Infinity Corrected Long Working Distance Objectives are world-renowned for setting the standard of excellence for long working distance microscope optics. They have achieved the best combination of working distance and optical performance by using a new approach—avoiding outdated conventions used by competitors. Making the objectives larger and longer has made the designs easier (95mm parfocalization length). The lenses are all Plano Apochromats to maintain as high an N.A. and contrast as possible. An apochromatic objective lens is chromatic aberration corrected for red, blue, and yellow, while a standard achromatic objective lens is only corrected for red and

blue. Plano Apochromats are typically very expensive, but high-volume production has made it possible to keep the cost down comparative to standard Achromat long working distance objectives. Mitutoyo Infinity Corrected Long Working Distance Objectives are optimized for bright field illumination (incident illumination parallel to the optical axis) and are ideal for in-line illumination applications. A secondary (or tube) lens is required for an infinity correction system. All stated magnifications are based on a tube lens focal length of 200mm. Mounting thread: M26 x0.706 pitch (36 TPI).

M Plan Apo SL Series


- Super-Long Working Distance for Bright Field Inspection
- 13mm Working Distance for 100X and 200X Models
- High Quality Apochromat Design
- Flat Image Surface over Entire Field of View
- Good Color Reproducibility

Accessory Tube Lenses

Accessory Tube Lenses and C-Mount Thread Adapters can be used to adapt the Mitutoyo objectives to additional configurations.

Edmund Optics is the main source for Mitutoyo Objectives. Place your orders now for these in demand quality products.

Technical Information



Stock No.	M Plan Apo	A	B	C	D	E	F	W.D.
#58-235	1X	84.0	-	38.0	-	41.0	34.0	11.0
#46-142	2X	61.0	1.4	27.5	24.7	32.2	34.0	34.0
#46-143	5X	61.0	1.6	25.0	23.0	32.2	34.0	34.0
#66-383	7.5X	60.0	-	25.0	24.0	32.2	34.0	35.0
#46-144	10X	61.0	2.0	28.2	-	32.2	34.0	34.0
#46-145	20X	75.0	1.5	29.2	-	32.2	34.0	20.0
#46-146	50X	82.0	1.5	29.2	-	32.2	34.0	13.0
#46-147	100X	89.0	4.7	29.2	17.8	32.2	34.0	6.0
Stock No.	M Plan Apo HR	A	B	C	D	E	F	W.D.
#34-247	5XHR	69.5	3.7	24.8	-	32.2	34.0	25.5
#58-236	10XHR	80.0	7.5	29.0	26.0	37.0	39.0	15.0
#58-237	50XHR	89.8	2.0	28.2	-	32.2	34.0	5.2
#58-238	100XHR	93.7	2.0	28.2	-	32.2	34.0	1.3
Stock No.	M Plan APO SL	A	B	C	D	E	F	W.D.
#46-398	20XSL	64.5	1.5	24.8	24.0	32.2	34.0	30.5
#46-399	50XSL	74.5	3.9	25.2	23.5	32.2	34.0	20.5
#46-401	100XSL	82.0	1.4	23.9	22.0	32.2	34.0	13.0

