

[See all 11 Products in Family](#)

## 200µm 0.22 NA UV/VIS Fiber, 10m Length



Stock **#57-068** CLEARANCE **7 In Stock**

€81<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€81,50 each
Qty 5+	€72,50 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Note:**

Fiber ends are not polished.

### Physical & Mechanical Properties

Cladding Diameter (µm):  
220 ±4

<b>Minimum Bend Radius (mm):</b>	
44/22 (Continuous/Momentary)	
<b>Length (m):</b>	
10.00	
<b>Outer Diameter (μm):</b>	
239 ±5	
<b>Core Diameter (μm):</b>	
200 ±4	
<b>Optical Properties</b>	
<b>Acceptance Angle (°):</b>	
25.4	
<b>Coating:</b>	
UV/MS	
<b>Substrate:</b> <input type="checkbox"/>	
Fused Silica	
<b>Numerical Aperture NA:</b>	
0.22	
<b>Index of Refraction (n<sub>1</sub>) - Core:</b>	
1.457	
<b>Index of Refraction (n<sub>1</sub>) - Cladding:</b>	
1.439	
<b>Wavelength Range (nm):</b>	
190 - 1250	
<b>Numerical Aperture (NA) Tolerance:</b>	
±0.02	
<b>Material Properties</b>	
<b>Buffer Material:</b>	
Polyimide	
<b>Environmental &amp; Durability Factors</b>	
<b>Operating Temperature (°C):</b>	
-190 to +390	
<b>Regulatory Compliance</b>	
<b>RoHS 2015:</b>	
<a href="#">Compliant</a>	
<b>Reach 209:</b>	
<a href="#">Compliant</a>	
<b>Certificate of Conformance:</b>	
<a href="#">View</a>	

## Product Details

### UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

### VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50μm – 600μm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600μm.

**Note:** Fiber ends are not polished.

## Technical Information

