

**TECHSPEC® 20mm 532nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #48-573 **14 In Stock**

⊖ 1 ⊕ €316.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€316,00 each
Qty 6-25	€256,00 each
Qty 26-99	€233,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Linear Polarizer **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

**Clear Aperture (%):**

90.00

**Construction:**

Cube

**Dimensions (mm):**

20.0 x 20.0 x 20.0 ±0.1

**Optical Properties**

**Beam Deviation (arcmin):**

±3

**Coating Specification:**

R<sub>abs</sub> <0.25% @ 532nm

**Design Wavelength DWL (nm):**

532

**Extinction Ratio:**

1000:1

**P-Polarization Transmission (%):**

>95

**S-Polarization Reflection (%):**

>99.5

**Substrate:**

**N-BK7**

**Surface Quality:**

40-20

**Power (fringes) @ 632.8nm:**

1.25

**Irregularity (fringes) @ 632.8nm:**

0.25

**Regulatory Compliance**

**RoHS 2015:**

**Compliant**

**Reach 219:**

**Compliant**


**Certificate of Conformance:**

**View**

**Product Details**

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision **right angle prisms** cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.



**Technical Information**

