

TECHSPEC® 20mm Dia., 1mm Thick, NIR II Coated, $\lambda/4$ Fused Silica Window



TECHSPEC® $\lambda/4$ UV Fused Silica Windows

Stock #72-351 5 In Stock

-

1

+

€147⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€147,00 each
Qty 6-25	€118,00 each
Qty 26-49	€110,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):

18.00

Diameter (mm):

20.00 +0.00/-0.10	
1.00 ±0.10	Thickness (mm):
<1	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
522.00	Knoop Hardness (kg/mm²):

Optical Properties

NIR II (750-1550nm)	Coating:
Fused Silica (Corning 7980)	Substrate: ☐
1.458	Index of Refraction (n _d):
40-20	Surface Quality:
λ/4	Transmitted Wavefront, P-V:
67.8	Abbe Number (v _d):
R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
750 - 1550	Wavelength Range (nm):

8 J/cm² @ 1064nm, 10ns	Damage Threshold, Reference:
------------------------	------------------------------

Material Properties

2.20	Density (g/cm³):
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Available Uncoated or BBAR Coated for UV, Visible, and NIR
- Ideal for Imaging Applications
- Circular and Rectangular Sizes from 5 to 200mm
- 1λ or λ/10 UV Fused Silica Windows Also Available

TECHSPEC® λ/4 UV Fused Silica Windows are manufactured with 40-20 surface quality and λ/4 transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC λ/4 UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

Technical Information



FUSED SILICA																															
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92.5</td></tr><tr><td>400</td><td>94.0</td></tr><tr><td>600</td><td>94.0</td></tr><tr><td>800</td><td>94.0</td></tr><tr><td>1000</td><td>94.0</td></tr><tr><td>1200</td><td>94.0</td></tr><tr><td>1400</td><td>92.0</td></tr><tr><td>1600</td><td>94.0</td></tr><tr><td>1800</td><td>94.5</td></tr><tr><td>2000</td><td>94.5</td></tr><tr><td>2200</td><td>90.0</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	92.5	400	94.0	600	94.0	800	94.0	1000	94.0	1200	94.0	1400	92.0	1600	94.0	1800	94.5	2000	94.5	2200	90.0	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data						
Wavelength (nm)	Transmission T (%)																														
200	92.5																														
400	94.0																														
600	94.0																														
800	94.0																														
1000	94.0																														
1200	94.0																														
1400	92.0																														
1600	94.0																														
1800	94.5																														
2000	94.5																														
2200	90.0																														
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>93.0</td></tr><tr><td>400</td><td>96.0</td></tr><tr><td>600</td><td>96.0</td></tr><tr><td>800</td><td>95.5</td></tr><tr><td>1000</td><td>95.5</td></tr><tr><td>1200</td><td>95.5</td></tr><tr><td>1400</td><td>93.0</td></tr><tr><td>1600</td><td>95.5</td></tr><tr><td>1800</td><td>95.5</td></tr><tr><td>2000</td><td>95.5</td></tr><tr><td>2200</td><td>90.0</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	93.0	400	96.0	600	96.0	800	95.5	1000	95.5	1200	95.5	1400	93.0	1600	95.5	1800	95.5	2000	95.5	2200	90.0	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data						
Wavelength (nm)	Transmission T (%)																														
200	93.0																														
400	96.0																														
600	96.0																														
800	95.5																														
1000	95.5																														
1200	95.5																														
1400	93.0																														
1600	95.5																														
1800	95.5																														
2000	95.5																														
2200	90.0																														
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75.0</td></tr><tr><td>250</td><td>99.0</td></tr><tr><td>300</td><td>99.5</td></tr><tr><td>400</td><td>99.0</td></tr><tr><td>500</td><td>99.5</td></tr><tr><td>600</td><td>99.5</td></tr><tr><td>800</td><td>98.0</td></tr><tr><td>1000</td><td>90.0</td></tr><tr><td>1200</td><td>80.0</td></tr><tr><td>1400</td><td>78.0</td></tr><tr><td>1600</td><td>76.0</td></tr><tr><td>1800</td><td>75.5</td></tr><tr><td>2000</td><td>75.5</td></tr><tr><td>2200</td><td>76.0</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75.0	250	99.0	300	99.5	400	99.0	500	99.5	600	99.5	800	98.0	1000	90.0	1200	80.0	1400	78.0	1600	76.0	1800	75.5	2000	75.5	2200	76.0	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																														
200	75.0																														
250	99.0																														
300	99.5																														
400	99.0																														
500	99.5																														
600	99.5																														
800	98.0																														
1000	90.0																														
1200	80.0																														
1400	78.0																														
1600	76.0																														
1800	75.5																														
2000	75.5																														
2200	76.0																														

	
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 350 - 450\text{nm}$ $R_{avg} \leq 1.5\% @ 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

