

20mm Dia. Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock **#70-252** **20+ In Stock**

-

1

+

€49^{.50}

ADD TO CART

Volume Pricing	
Qty 1-10	€49,50 each
Qty 11-49	€39,50 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Opal Diffuser	Type:
Physical & Mechanical Properties	
20.00 ±0.50	Diameter (mm):
120	Grit:

1.75 ±0.10	Thickness (mm):
Optical Properties	
Uncoated	Coating:
White Diffusing Glass	Substrate: ☐
400 - 1100	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.