

TECHSPEC®

20mm Dia. x 20mm FL, NIR I Inked, Double-Convex Lens



Stock **#63-646-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€54,00

ADD TO CART

Qty 1-9
€54,00
Qty 10+
€48,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Back Focal Length BFL (mm):

18.55
Effective Focal Length EFL (mm): 20.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.60
Radius R₁=R₂ (mm): 30.25
Clear Aperture CA (mm): 19.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View