

TECHSPEC® 2.0mm Dia. x 3.0mm FL, Uncoated, Plano-Convex Lens



Stock **#65-255** 3-4 DAYS

[Other Coating Options](#)

− 1 + **€64,00**

ADD TO CART

Qty 1-9
€64,00
Qty 10+
€57,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
2.00 +0.0/-0.025

Effective Focal Length EFL (mm):

3.00 @ 587.6nm
Back Focal Length BFL (mm): 2.57
Coating: Uncoated
Substrate: N-LASF9
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.60
Radius R₁ (mm): 2.55
Clear Aperture CA (mm): 1.5
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View