


20mm Dia x 40mm Focal Length, Spherical Mirror



Stock **#46-238** 16 In Stock

-

1

+

€53^{.50}

ADD TO CART

Volume Pricing	
Qty 1-49	€53,50 each
Qty 50-99	€49,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

20.00 +0.00/-0.30

Diameter (mm):

Ground

Back Surface:

3.00	Center Thickness CT (mm):
±0.30	Center Thickness Tolerance (mm):
3.63	Edge Thickness ET (mm):
Ground	Edges:
80.0	Radius R (mm):

Optical Properties

N-BK7	Substrate: ☐
±2	Focal Length Tolerance (%):
60-40	Surface Quality:
λ/4	Surface Accuracy:
40.00	Effective Focal Length EFL (mm):
80.00	Radius of Curvature (mm):
f/2	Aperture (f/#):
Protected Aluminum (400-2000nm)	Coating:
R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm	Coating Specification:
Metal	Coating Type:
400 - 2000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Aluminum Coating
- Ideal for UV, Visible, and IR Applications
- Multiple Diameter and f/# Combinations Available

λ/4 Spherical Mirrors have flat rear surfaces and aluminum coated spherical front surfaces. These mirrors are ideal for applications in UV, VIS, and IR wavelength ranges.

Technical Information

