

TECHSPEC[®] 20mm UV-VIS Coated, Fused Silica Right Angle Prism



Stock #27-337 2 In Stock

-

1

+

€151^{,00}

ADD TO CART

Volume Pricing	
Qty 1-5	€151,00 each
Qty 6-25	€121,00 each
Qty 26-49	€113,25 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Right Angle Prism

Type:

Coating on Entrance/Exit Faces

Note:

Physical & Mechanical Properties

+0.00/-0.10

Dimensional Tolerance (mm):

	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Length of Hypotenuse (mm):
28.30	

	Length of Legs (mm):
20.00	

Optical Properties

	Angle Tolerance (arcsec):
±15	

	Coating:
UV-VIS (250-700nm)	

	Substrate: ☐
Fused Silica (Corning 7980)	

	Surface Quality:
40-20	

	Image Orientation:
Left-Handed	

	Coating Specification:
R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm	

	Ray Deviation (°):
90	

	Wavelength Range (nm):
250 - 700	

	Damage Threshold, Reference: ☐
3 J/cm ² @ 355nm, 10ns 5 J/cm ² @ 532nm, 10ns	

	Power (fringes) @ 632.8nm:
1.25	

	Irregularity (fringes) @ 632.8nm:
0.20	

Regulatory Compliance

	RoHS 2015:
Compliant	

	Certificate of Conformance:
View	

	Reach 235:
Compliant	

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- BBAR Coatings from the UV to the NIR
- Ideal for Low Power Laser Sources
- Sizes Ranging from 5 – 25mm

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Fused Silica Right Angle Prisms bend an image path or redirect light at 90°. Featuring a broadband antireflection (BBAR) coating on both the entrance and exit surfaces, these prisms provide improved transmission efficiency compared to uncoated [UV fused silica right angle prisms](#). Manufactured from UV fused silica, these prisms feature low thermal expansion and excellent transmission through the UV, visible, and NIR spectra. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Fused Silica Right Angle Prisms are ideal for use in a wide range of scientific and industrial applications including medical devices, semiconductor inspection, and laser-based instrumentation.