

[See all 7 Products in Family](#)

TECHSPEC[®]

20X, 0.19 NA, UCf Objective



Stock **#26-690** **17 In Stock**

-

1

+

€366^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	€366,00 each
Qty 3-4	€341,00 each
Qty 5-9	€329,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fluorite	Type:
Finite Conjugate	Style:
Manufacturer:	

Physical & Mechanical Properties

158.51	Length (mm):
29	Maximum Diameter (mm):
139	Weight (g):

Optical Properties

0.44	Horizontal Field of View, 2/3" Sensor:
0.704	Horizontal Field of View, 1.1" Sensor:
8.00	Focal Length FL (mm):
20X	Magnification:
0.19	Numerical Aperture NA:
3.51	Resolving Power (µm):
7.42	Depth of Field (µm):
7.7	Working Distance (mm):
400 - 700	Wavelength Range (nm):
17.6	Field Number (mm):

Sensor

1.1"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

C-Mount	Mounting Threads:
---------	-------------------

Environmental & Durability Factors

+10 to +40	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Compact Finite Conjugate Objectives
 - Mount Directly to a C-Mount Camera
 - Near Diffraction Limited performance
- TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.