

20X ZEISS A-Plan Objective

See More by [ZEISS](#)



ZEISS A-Plan Objectives



Stock **#13-817** 12 In Stock

-

1

+

€387⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€387,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
421050-9900-000	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm	

Microscope Objective	Type:
----------------------	-------

Fluorescence, BrightField	Typical Applications:
Infinity Corrected	Style:
Zeiss	Manufacturer:
Physical & Mechanical Properties	
1.15	Field of View (mm):
44.40	Length excluding Threads (mm):
30	Maximum Diameter (mm):
130	Weight (g):
Optical Properties	
0.17	Compatible Cover Glass Thickness (mm):
8.20	Focal Length FL (mm):
20X	Magnification:
0.45	Numerical Aperture NA:
0.61	Resolving Power (µm):
1.36	Depth of Field (µm):
0.46	Working Distance (mm):
480 - 650	Wavelength Range (nm):
23	Field Number (mm):
45.06	Parfocal Length (mm):
N/A	Immersion Liquid:
Threading & Mounting	
M27 x0.75	Mounting Threads:
Environmental & Durability Factors	
+10 to +40	Operating Temperature (°C):
75% at 35°C	Operating Humidity:
Regulatory Compliance	
View	Certificate of Conformance:


Product Details

- Ideal for Brightfield and Fluorescence Applications
- Excellent Color Correction and Flatness of Field
- Oil Immersion Options Available

ZEISS A-Plan Plan Achromat Infinity Corrected Objectives are designed for a variety of routine life science applications. These objectives exhibit excellent color correction and flatness of field that satisfy ISO 19012-1:2013 standards. They are ideal for brightfield inspection of fixed and stained tissues or cells in fluorescence applications. The large field number of 23mm facilitates fast screening of samples. ZEISS A-Plan Plan Achromat Infinity Corrected Objectives are corrected for standard cover slips with 0.17mm thickness.

Note: Tube Lens [#13-828](#) is required when using ZEISS A-Plan Plan Achromat Infinity Corrected Objectives with non-ZEISS Infinity Color Corrected (ICS) microscope systems.

Technical Information



Stock No.	A-Plan	A	B	C	D	E	F	G	W.D.	PFL	Mounting Threads
#13-814	2.5X	34.5	6.25	2.75	17.0	22.5	30.0	3.9	10.40	45.06	M27x0.75
#13-815	5X	34.8	7.25	2.75	17.0	22.5	30.0	3.9	10.10	45.06	M27x0.75
#13-816	10X	40.4	4.75	5.25	12.0	22.5	30.0	3.9	4.50	45.06	M27x0.75
#13-817	20X	44.4	7.90	6.30	6.4	22.0	30.0	4.0	0.46	45.06	M27x0.75
#13-818	40X	44.4	8.00	3.30	7.0	21.0	30.0	4.0	0.45	45.06	M27x0.75
#13-819	63X	44.6	8.00	6.60	7.0	22.0	30.0	4.0	0.30	45.06	M27x0.75
#13-820	100X	43.9	10.70	3.20	7.1	19.0	30.0	3.9	0.97	45.06	M27x0.75
#13-821	100X OIL	44.7	9.00	5.70	7.0	19.0	30.0	4.0	0.22	45.06	M27x0.75