

24mm FL Wide Angle Large Format F-Mount Lenses



Wide Angle Large Format F-Mount Lenses

Stock **#14-262** **5 In Stock**

-

1

+

€1.260⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.260,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Wide Angle Large Format F-Mount Lenses	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
	Length (mm):

95.00	
83	Maximum Diameter (mm):
83	Outer Diameter (mm):
565	Weight (g):

Optical Properties	
84.1°	Horizontal Field of View, 35mm Sensor:
61.8°	Horizontal Field of View, APS-C Sensor:
43.30	Maximum Image Circle (mm):
24.00	Focal Length FL (mm):
110 - ∞	Working Distance (mm):
f/1.4 - f/22	Aperture (f/#):
<4	Distortion (%):
<4	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor	
35mm (43.3mm Image Circle)	Maximum Sensor Format:

Threading & Mounting	
M77 x0.75	Filter Thread:
F-Mount	Mount:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 43.3mm Diagonal (35mm Full Frame) Large Format Sensor
- Wide Angles and Large Fields of View
- Lockable Manual Focus and Iris
- 8mm to 24mm Focal Length

Wide Angle Large Format F-Mbunt Lenses are designed with ultra large fields of view for mid and large format sensors and are ideal for applications requiring short focal lengths. The 8mm focal length lens is designed for creating a fisheye image on APS-C (27.9mm diagonal) sensors, enabling large objects to be in focus throughout the field of view with limited refocusing. Both the 14mm and 24mm focal length lenses are designed for 35mm (43.3mm diagonal) large format sensors. The 14mm lens is versatile with superb image quality even at its full f/2.8 aperture, while the 24mm lens features a fast f/1.4 aperture. Wide Angle Large Format F-Mbunt Lenses have multi-layer AR coatings to minimize flare and ghosting to ensure excellent image quality and contrast. Each lens features a lockable manual focus and iris.