

TECHSPEC® 22 x 22mm UV Enhanced Aluminum, λ/4 Mirror



Stock #46-718 [CONTACT US](#)

⊖ 1 ⊕ **€55,00**

ADD TO CART

Qty 1-5

€55,00

Qty 6+

€44,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):

λ/4

Substrate:

[BOROFLOAT®](#)

Back Surface:

Commercial Polish

Surface Quality:
60-40

Dimensions (mm):
22.0 x 22.0

Dimensional Tolerance (mm):
+0.0/-0.5

Coating Specification:
R_{avg} >89% @ 250 - 450nm
R_{avg} >85% @ 250 - 700nm

Coating:
Enhanced Aluminum (250-700nm)

Coating Type:
Metal

Bevel:
Protective bevel as needed

Clear Aperture (%):
85

Edges:
Fine Ground

Thickness (mm):
5.00 +0.5/-0.0

Type:
Flat Mirror

Wavelength Range (μm):
0.25 - 0.7

Wavelength Range (nm):
250 - 700

Length (mm):
22.00

Width (mm):
22.00

Damage Threshold, Reference: □
0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)