



25 x 25mm, 0.25mm Spacing, Glass Distortion Target



Stock **#58-527** CLEARANCE **2 In Stock**

-

1

+

€669⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€669,50 each
Qty 5+	€636,75 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Chrome on Glass

Type:

NIST Certification: Serialized NIST Traceable Certificate Included	
Physical & Mechanical Properties	
0.125	Dot Diameter (mm):
0.250	Dot Spacing (mm):
±0.002	Overall Accuracy (mm):
25 x25	Pattern Size (mm):
2 x2	Dimensions (inches):
1.50	Thickness (mm):
± 0.002	Dot Diameter Tolerance (mm):
± 0.002 Center to Center	Dot Spacing Tolerance (mm):
0.001	Flatness (inches):
Optical Properties	
Reflective First Surface Chromium R _{abs} = 50% ±5% @ 550nm	Coating:
Soda Lime Float Glass	Substrate:
>3.0	Optical Density OD (Average):
40-20	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- For Distortion Measurement and Calibration of Imaging Systems
- Chrome on Soda Lime Glass or Chrome on White Ivory Glass Versions
- NIST Certificate of Accuracy Included

Fixed Frequency Grid Distortion Targets are used to resolve the often-troublesome distortion factor in measurement applications. It is important to note that no information about the object is actually lost, but merely misplaced in the image when distortion occurs. Using these targets, one can easily determine the precise amount of distortion present and back it out of measurements. The dot center can be located using blob (or centroid) analysis in measurement software. Fixed Frequency Grid Distortion Targets are available in various options each with different dot size/dot frequency combinations. Choose a target based on your field of view or resolution/accuracy requirements. These targets are available in either a chrome on soda lime glass or chrome on white ivory glass to accommodate transmission or reflection-based applications, respectively. Included in the packaging is a serialized NIST Traceable Certificate of Accuracy per ML-STD-45662A