

TECHSPEC<sup>®</sup> 25.0mm Dia. x -200 FL, VIS-NIR, UV Plano-Concave Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock #21-058 [CONTACT US](#)

[Other Coating Options](#)

-

1

+

 €164<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €164,00 each                  |
| Qty 6-25       | €131,00 each                  |
| Qty 26-49      | €123,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Concave Lens

Type:

Max. Flat Annulus is 0.3mm

Note:

| Physical & Mechanical Properties |                                  |
|----------------------------------|----------------------------------|
| 25.00 +0.0/-0.025                | Diameter (mm):                   |
| 2.50                             | Center Thickness CT (mm):        |
| ±0.10                            | Center Thickness Tolerance (mm): |
| <1                               | Centering (arcmin):              |
| 24                               | Clear Aperture CA (mm):          |
| 3.32                             | Edge Thickness ET (mm):          |

| Optical Properties                                                                                                 |                                                       |
|--------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| -200.00                                                                                                            | Effective Focal Length EFL (mm):                      |
| Fused Silica (Corning 7980)                                                                                        | Substrate: <input type="checkbox"/>                   |
| 8.00                                                                                                               | f/#:                                                  |
| 0.06                                                                                                               | Numerical Aperture NA:                                |
| VIS-NIR (400-1000nm)                                                                                               | Coating:                                              |
| 400 - 1000                                                                                                         | Wavelength Range (nm):                                |
| -201.71                                                                                                            | Back Focal Length BFL (mm):                           |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm | Coating Specification:                                |
| 587.6                                                                                                              | Focal Length Specification Wavelength (nm):           |
| ±1                                                                                                                 | Focal Length Tolerance (%):                           |
| -91.69                                                                                                             | Radius R <sub>1</sub> (mm):                           |
| 40-20                                                                                                              | Surface Quality:                                      |
| 5 J/cm² @ 532nm, 10ns                                                                                              | Damage Threshold, Reference: <input type="checkbox"/> |
| 1.5λ                                                                                                               | Power (P-V) @ 632.8nm:                                |
| λ/4                                                                                                                | Irregularity (P-V) @ 632.8nm:                         |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Wavelength Range of 200 - 2200nm
- Popular UV-AR Coating Option Available

TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses are high performance UV optic elements, manufactured utilizing state of the art CNC equipment. Zygo's GPI-XP Interferometer is used to assure the surface accuracy and performance of these UV optics. UV Grade lenses are precision manufactured using research-grade synthetic fused silica. In addition to providing excellent transmission characteristics and higher operating temperatures, synthetic fused silica also exhibits an exceptional inclusion specification and chemical purity. TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses are an ideal choice for many laser and imaging applications, particularly those involving ultraviolet wavelengths. A broadband anti-reflection coating is available for optimized throughput in the ultraviolet spectrum.

## Technical Information



UV FS Transmission Curve

| FUSED SILICA                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>Uncoated Fused Silica<br/>Typical Transmission</b></p>                     | <p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                                                                                                                                |
| <p><b>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</b></p> | <p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                   |
| <p><b>Fused Silica with UV-AR Coating<br/>Typical Transmission</b></p>           | <p>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\% @ 250 - 425\text{nm}</math><br/> <math>R_{avg} \leq 0.75\% @ 250 - 425\text{nm}</math><br/> <math>R_{avg} \leq 0.5\% @ 370 - 420\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

|                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <p data-bbox="573 278 1083 385"><b>Fused Silica with UV-VIS Coating</b><br/><b>Typical Transmission</b></p>       | <p data-bbox="1329 439 1854 489">Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p data-bbox="1329 501 1854 552">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1478 563 1705 614"><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div> <p data-bbox="1329 649 1854 700">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 712 1705 736"><a href="#">Click Here to Download Data</a></p>                                                                        |
| <p data-bbox="567 958 1089 1065"><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1329 1142 1854 1193">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1205 1854 1255">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1478 1267 1705 1291"><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <p data-bbox="1329 1302 1854 1353">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 1365 1705 1389"><a href="#">Click Here to Download Data</a></p>                                                                                                                          |
| <p data-bbox="571 1638 1085 1745"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 1780 1854 1831">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1329 1843 1854 1893">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1467 1905 1715 1979"><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <p data-bbox="1329 2015 1854 2065">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 2077 1705 2101"><a href="#">Click Here to Download Data</a></p> |
| <p data-bbox="569 2309 1087 2415"><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1329 2487 1854 2537">Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1329 2549 1854 2599">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1478 2611 1705 2635"><math>R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}</math></div> <p data-bbox="1329 2647 1854 2697">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 2709 1705 2733"><a href="#">Click Here to Download Data</a></p>                                                                                                                           |



