

TECHSPEC®

25.0mm Dia. x 750.0mm FL, NIR II, Inked, Plano-Convex Lens



Stock **#67-559-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€51,50

ADD TO CART

Qty 1-9
€51,50
Qty 10+
€46,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):

750.00 @587.6nm
Back Focal Length BFL (mm): 747.89
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.20 ±0.10
Edge Thickness ET (mm): 3.00
Radius R₁ (mm): 387.60
Clear Aperture CA (mm): 24
f/#: 30
Numerical Aperture NA: 0.02
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View