

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Silver Off-Axis Parabolic Mirrors](#)

[See all 23 Products in Family](#)

TECHSPEC®

25.4 x 203.2mm Off-Axis Parabolic Mirror

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Stock #36-593 **5 In Stock** [Other Coating Options](#)

- 1 +

€429⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€429,00 each
Qty 6-10	€385,00 each
Qty 11-25	€370,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- Zemax:zmx
- eDrawing:eprt
- Code V:seq
- EO Spec Sheet
- [Download All](#)

General

Type: Off-Axis Parabolic Mirror

Physical & Mechanical Properties

Y Offset (mm): 203.2

Diameter (mm): 25.40
+0.00/-0.38

Clear Aperture (%): 90

Surface Roughness (Å): <100 RMS

Optical Properties

Coating Type: Metal

Coating: Protected Silver (450-12000nm)

Off-Set Angle (°): 90

Wavelength Range (nm): 450 - 12000

Effective Focal Length EFL (mm): 203.20

Substrate: Aluminum 6061-T6

Coating Specification: R_{avg} ≥98% @ 2,000 - 12,000nm, R_{avg} (typical) 96% @ 450 - 2,000nm

Focal Length Tolerance (%): ±1

Parent Focal Length PFL (mm): 101.6

Surface Figure, RMS: λ/4

Surface Quality: 80-50

Radius of Curvature: 203.20

(mm):

Reflected Wavefront, RMS: $\lambda/2$

Threading & Mounting

Compatible Mounting Plates: [#47-111](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 247: **Compliant**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Protected Silver Coating for Visible and IR Application
- 100Å Surface Roughness
- 90° Offset Angle
- Aluminum and Gold Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are designed to direct and focus incident collimated light at a specific offset angle with minimal scatter loss. Coated with protected silver, these OAP mirrors provide high reflectivity from the visible to the infrared (IR), making them ideal for broadband applications. These Silver OAPs provide unobstructed access to the point of focus, allowing for the creation of more compact systems. TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are commonly used in instrumentation and laser systems in the visible and IR spectrum, including Schlieren, MTF, FLIR, and FTIR systems. For additional surface roughness options and offset angles, please see our aluminum or gold coated OAPs or [contact us](#) for custom options.

Technical Information

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Mounting Plate for 25.4mm Diameter Off-Axis Mirrors		#47-111	€135,00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>


Related Products



Aluminum Off-Axis Parabolic Mirrors



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.
Select Your Country/Region:



Laser Line Coated Off-Axis Parabolic (OAP) Mirrors

Frequently Purchased Together



#35-602 - 50.8 x 387.6mm EFL 15° Protected Gold 100Å Off-Axis Parabolic Mirror
€549,00

Qty



#88-954 - C-Mount Female to SM1 Male Step-Down Adapter
€59,50

Qty



#88-955 - C-Mount Male to SM1 Female Step-Up Adapter
€62,50

Qty



#35-539 - 25.4 x 387.6mm EFL 15° Protected Gold 100Å Off-Axis Parabolic Mirror
€399,00

Qty

Resources


Media Type

- Application Note
- Video
- FAQ
- Glossary




CASE STUDIES

Using IR Spectroscopy for Counterfeit Drug Detection




APPLICATION NOTE

Roughness of Diamond Turned Off-Axis Parabolic...




APPLICATION NOTE

Off-Axis Parabolic Mirror Selection...




VIDEO

Compound Parabolic Concentrators Review



FAQ

I would like to use your Off-Axis Mirror in a laser...



FAQ

How are your Off-Axis Metal Mirrors...

[View More](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: