


SCHOTT AS87ECO, 25.4 x 127mm, 0.1mm Thick, Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock #12-316 13 In Stock

-

1

+

€46⁰⁹

ADD TO CART

Volume Pricing	
Qty 1-10	€46,09 each
Qty 11-49	€37,08 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed	Bevel:
90	Clear Aperture (%):
22.86 x 114.30	Clear Aperture CA (mm):
25.40 x 127.00	Dimensions (mm):
0.10 ±0.01	Thickness (mm):
500.00	Knoop Hardness (kg/mm²):
0.22	Poisson's Ratio:
73.3	Young's Modulus (GPa):
127.00	Length (mm):
25.40	Width (mm):
Optical Properties	
59.5	Abbe Number (v _d):
Uncoated	Coating:
1.504	Index of Refraction (n _d):
AS 87 ECO	Substrate:
80-50	Surface Quality:
200 - 3200	Wavelength Range (nm):
Material Properties	
8.7	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.46	Density (g/cm³):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- High Level of Flexibility
- Ultra-Thin Thickness for Low Profile Designs
- Excellent Transmission from 250nm to >3µm

SCHOTT AS 87 ECO Ultra-Thin Wndows feature an extremely thin and flexible design for applications requiring a rugged, low profile. These windows have excellent mechanical properties, including a high bending and impact strength, minimizing the possibility of damage under normal operating conditions. They also provide excellent transmission from the UV to the IR, enabling integration into applications that range from biomedical to IR imaging. SCHOTT AS 87 ECO Ultra-Thin Windows are manufactured through a draw-down process that virtually eliminates surface defects and provides the glass surfaces with an extremely low surface roughness. Common applications include their use as a cover glass for displays, fingerprint sensors, and touch panels, where their high scratch resistance prevents surface damage.

QUOTE YOUR SIZE