

[See all 44 Products in Family](#)

TECHSPEC® 25.4 x 25.4mm x -75mm FL, VIS 0° Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-995** **2 In Stock**

⊖ 1 ⊕ €108⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€108,00 each
Qty 6-25	€99,00 each
Qty 26-49	€93,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cylinder Lens, Plano-Concave **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

Center Thickness CT (mm):

4.00

Center Thickness Tolerance (mm):

±0.1

Clear Aperture CA (mm):

22.86 x 22.86

Dimensional Tolerance (mm):

+0.0/-0.025

Dimensions (mm):

25.4 x 25.4

Edge Thickness ET (mm):

6.07

Axial Twist (arcmin):

<3

Optical Properties

Effective Focal Length EFL (mm):

-75.00

Substrate:

N-BK7

f/#:

3

Numerical Aperture NA:

0.08

Coating:

VIS 0° (425-675nm)

Wavelength Range (nm):

425 - 675

Back Focal Length BFL (mm):

-77.64

Coating Specification:

R_{avg} ≤ 0.4% @ 425 - 675nm

Radius R₁ (mm):

38.76

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

1.5λ

Irregularity (P-V) @ 632.8nm:

λ/4

Plano Axis Wedge (arcmin):

<5

Power Axis Wedge (arcmin):

<5

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:

Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Beam Shaping Grade Specifications
- Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
- Negative Focal Length

TECHSPEC® Imaging Grade PCV Cylinder Lenses are typically used to diverge collimated light in a single axis. These lenses are designed for system integration due to the tightly controlled specifications and generous volume discounts. TECHSPEC Imaging Grade PCV Cylinder Lenses feature tightly controlled wedge and tilt specifications and are ideal for circularizing elliptical beams in combination with our [TECHSPEC Imaging Grade PCX Cylinder Lenses](#).

Coating Curves
