


[See all 6 Products in Family](#)

254.0mm/10.0" Optic Dia., Gimbal Mount



Stock **#72-333** **1 In Stock**

- 1 + €5.350^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€5.350,00 each
Qty 5+	€5.082,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Circular	Type of Optics:
Three Spring-Loaded Clips	Optic Holding Style:


Type of Adjustment Screws:	
Micrometer	
Physical & Mechanical Properties	
Clear Aperture CA (mm):	
248.80	
Fine Tilt Angle (°):	
±5.0	
Fine Tip Angle (°):	
±5.0	
Max. Thickness of Compatible Optics (mm):	
55	
Optical Axis Height (mm):	
203.20	
Size of Compatible Optics (inches):	
10	
Optical Axis Height (inches):	
8	
Threading & Mounting	
Size of Compatible Optics (mm):	
254.00	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

Product Details

- Gimbal Movement for Precision Tip and Tilt Alignment
- Compatible with 4", 4.25", 6", 8", 10" and 12" Diameter Optics
- Designed for Flat Mirrors
- Direct Mounting to English and Metric Breadboards for System Integration
- [Precision Gimbal Mounts](#) for Smaller Optics Also Available

Large Diameter Gimbal Optical Mirror Mount are ideal for integrating large diameter precision mirrors or other optical components into OEM and benchtop systems. These gimbal mirror mounts are compatible with 4.25" (with an included adapter for 4"), 6", 8", 10" and 12" diameter optics. Gimbal movement centers the axes of rotation on the optical surface, which when combined with micrometer driven precision tip and tilt adjustment, allows for accurate control of the beam path. Large Diameter Gimbal Optical Mirror Mounts feature mounting slots for direct breadboard mounting at either parallel to or 45° to the beam path. The mounting slots are compatible with both M6 and ¼"-20 mounting hardware.

Technical Information



Dimensions					
Optic Diameter (mm)	Optic Diameter (inches)	Clear Aperture (mm)	Max. Optic Thickness (mm)	Optical Axis Height (inches)	Optical Axis Height (mm)
	A	B	C	D	D
101.6/108.0	4/4.25	92	20	3.5	88.9
152.4	6	140	30	4.5	114.3
203.2	8	190	40	6.25	158.8
254.0	10	248.80	55	8	203.20
304.8	12	298.80	55	9	228.60