

[See all 1 Products in Family](#)

25.4mm Dia., 2mm Thick, ISP Optics Gold Dichroic Beamsplitter

See More by [ISP Optics](#)



Stock #25-033 CLEARANCE CONTACT US

⊖ 1 ⊕ €351⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€351,00 each
Need More?	Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Standard Beamsplitter **Type:**
BSP-DI-25-2 **Model Number:**

Physical & Mechanical Properties

85 **Clear Aperture (%):**
Construction:

Plate	
25.40 +0.00/-0.13	Diameter (mm):
<3	Parallelism (arcmin):
2.00 ±0.13	Thickness (mm):
Optical Properties	
S1: Beamsplitter Coating T _{avg} = 70% from 400 - 700nm R _{avg} = 95% from 3 - 12μm	Coating:
R _{avg} >95% @ 3000 - 12000nm and T _{avg} >70% @ 400 - 700nm	Coating Specification:
3000 - 12000	Reflection Wavelength (nm):
N-BK7	Substrate: <input type="checkbox"/>
M4 @ 633nm	Surface Flatness (P-V):
60-40	Surface Quality:
400 - 700	Transmission Wavelength (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Separate Visible Light from Infrared (3-12μm) Light
- Visible Transmitting/Infrared Reflecting and Visible Reflecting/Infrared Transmitting Designs
- Ideal for Combining Visible Guide Lasers with MMR Lasers

ISP Optics Infrared (IR) Dichroic Beamsplitters are used to separate visible light from infrared light, working deeper in the infrared than conventional hot and cold mirrors. The platinum dichroic beamsplitters reflect visible light while transmitting light between 3 – 12μm and have an Anti-Reflection (AR) coating on the back surface to increase throughput. The gold dichroic beamsplitters transmit visible light while reflecting infrared light between 3 – 12μm and can be used with an AOI from 0 to 45°. ISP Optics Infrared (IR) Dichroic Beamsplitters are ideal for combining guide lasers with mid-IR laser sources, such as QCL lasers, for applications including gas detection, mid-infrared photothermal microscopy, and infrared spectroscopy.