

TECHSPEC® 25.4mm Dia. 400 - 750nm Broadband $\lambda/10$ Mirror



Stock **#39-212** **20+ In Stock**

⊖ 1 ⊕ €115⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€115,00 each
Qty 6-25	€92,00 each
Qty 26-49	€86,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.00/-0.10

6.35 ±0.20 **Thickness (mm):**

Commercial Polish **Back Surface:**

90 **Clear Aperture (%):**

Ground, 0.5mm max bevel **Edges:**

<3 **Parallelism (arcmin):**

Optical Properties

Dielectric **Coating Type:**

Dielectric Mirror (400-750nm) **Coating:**

M10 **Surface Flatness (P-V):**

400 - 750 **Wavelength Range (nm):**

Fused Silica (Coming 7980) **Substrate:**

0-45 **Angle of Incidence (°):**

Coating Specification:
R_{avg} >98% @400 - 750nm (0 - 45°)
R_{avg} >99% @400 - 750nm (0°)

20-10 **Surface Quality:**

Damage Threshold, Reference:
0.5 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 209:**

View **Certificate of Conformance:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric M10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric M10 Mirrors are designed for applications from the UV to the near-infrared spectra.

Technical Information



Compatible Mounts

;