


[See all 2 Products in Family](#)

25.4mm Dia., 4mm Thick, 3° BBAR (2000-5000nm) Coated, ISP Optics Calcium Fluoride (CaF₂) Wedged Window

See More by [ISP Optics](#)



Calcium Fluoride (CaF₂) Wedged Windows

Stock #23-850 **4 In Stock**

⊖ 1 ⊕ €323.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€323,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**
Crystal **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

21.59

Diameter (mm):

25.40 +0.0/-0.13

Thickness (mm):

3.00 ±0.13

Bevel:

Protective as needed

Clear Aperture (%):

85

Edges:

Fine Ground

Poisson's Ratio:

0.26

Young's Modulus (GPa):

75.8

Knoop Hardness (kg/mm²):

158.30

Optical Properties

Coating:

BBAR (2000-5000nm)

Substrate:

[Calcium Fluoride \(CaF₂\)](#)

Index of Refraction (n_d):

1.495

Surface Quality:

60-40

Abbe Number (v_d):

94.99

Axis Orientation:

Random

Coating Specification:

R_{avg} <1.5% @ 2000-5000nm

R_{abs} <3.0% @ 2000-5000nm

R_{avg} <1.75% @ 2000-4000nm

Wavelength Range (nm):

2000 - 5000

Surface Flatness (P-V):

2λ @ 633nm

Wedge Angle (°):

3° ±0.25

Material Properties

Density (g/cm³):

3.18

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

18.85

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- 30 Arcmin Wedge
- Low Absorption, High Transmission
- Ideal for Harsh Environments
- [Precision Flat Calcium Fluoride Windows](#) Also Available

ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature a 30 arcmin wedge to eliminate fringe patterns from etalon effects and to prevent cavity feedback. Calcium fluoride's combination of low absorption and high damage

threshold make these windows a popular choice for free-space lasers. Its low refractive index allows it to be used without an anti-reflective coating. ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature low water solubility and offer superior hardness compared to other fluoride-based substrates, making them suitable for laser applications in harsh environments. Calcium Fluoride (CaF₂) Wedged Windows provide laser output protection from environmental effects and are ideal for beam sampling applications.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools