


[See all 4 Products in Family](#)

# 25.4mm Dia., 4mm Thick, 30' Wedge, ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Window | BF-WW-25-4

See More by [ISP Optics](#)



Barium Fluoride (BaF<sub>2</sub>) Wedged Windows



Stock **#16-806** **CLEARANCE** **6 In Stock**

− 1 + €389<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	€389,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

BF-WW-25-4 **Model Number:**

Protective Window **Type:**

## Physical & Mechanical Properties

21.59 **Clear Aperture CA (mm):**

**Diameter (mm):**

25.40 +0.00/-0.13

**Thickness (mm):**

4.00 ±0.13

**Bevel:**

Protective as needed

**Clear Aperture (%):**

85

**Edges:**

Fine Ground

**Poisson's Ratio:**

0.34

**Young's Modulus (GPa):**

53

**Knoop Hardness (kg/mm<sup>2</sup>):**

82.00

**Wedge Angle (arcmin):**

30±15 arcmin

## Optical Properties

**Coating:**

Uncoated

**Substrate:**

[Barium Fluoride \(BaF<sub>2</sub>\)](#)

**Index of Refraction (n<sub>d</sub>):**

1.478 @ 0.5µm  
1.451 @ 5µm  
1.401 @ 10µm

**Surface Quality:**

60-40

**Abbe Number (v<sub>d</sub>):**

81.78

**Wavelength Range (nm):**

200 - 12000

**Surface Flatness (P-V):**

2λ @ 633nm

## Material Properties

**Density (g/cm<sup>3</sup>):**

4.89

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

18.1

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 240:**

[Compliant](#)

## Product Details

- 30 Arcmin Wedge
- Excellent Transmission from 200nm - 12µm
- Resistant to High-Energy Radiation
- [Precision Flat Barium Fluoride \(BaF<sub>2</sub>\) Windows](#) Also Available

ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows feature a 30 arcmin wedge to eliminate etalon effects, improving readout in detection and spectroscopy applications. With a low index of refraction of 1.48, these windows provide high transmission from 200nm to 12µm without the need of an anti-reflection (AR) coating. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the vacuum ultraviolet range. ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows are ideal for infrared spectroscopy, thermal imaging, and general UV-IR detection applications. Barium fluoride is also a fast scintillator and can be used for the detection X-rays, gamma rays, or other high energy particles.

**Note:** These optical windows are very sensitive to thermal shock.

## Technical Information

