

25.4mm Dia., 532nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#39-171** **1 In Stock**

-

1

+

€655⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€655,00 each
Qty 11+	€610,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
High Energy Waveplate	Type:
Physical & Mechanical Properties	
18.0	Clear Aperture CA (mm):
25.40	Diameter (mm):

+0/-0.2	Dimensional Tolerance (mm):
Optically Bonded on UVFS (C7980) Substrate	Construction:
<3	Parallelism (arcsec):
Optical Properties	
R _{avg} <0.2%	Coating:
532	Design Wavelength DWL (nm):
Crystalline Quartz	Substrate: ☐
λ/2	Retardance:
20-10	Surface Quality:
<λ/10 @ 632.8nm	Transmitted Wavefront, P-V:
λ/250 @ 20°C	Retardance Tolerance:
>20 J/cm² @ 1064nm, 10ns, 10Hz	Damage Threshold, By Design: ☐
0	Retardance Order:
Threading & Mounting	
6 ±0.2	Mount Thickness (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Damage Threshold up to >20 J/cm² @ 1064nm
 - λ/4 and λ/2 Retardance
 - Black Anodized Aluminum Mount
 - UV to NIR Design Wavelengths Available
- High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.