

[See all 3 Products in Family](#)

**TECHSPEC® 25.4mm Dia., 6.35mm Thick, 1064nm, Nd:YAG IBS Laser Line Window**



TECHSPEC® IBS Laser Line Windows

Stock **#12-989** **20+ In Stock**

⊖ 1 ⊕ €148<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€148,00 each
Qty 6-25	€122,00 each
Qty 26-49	€114,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Line Window **Type:**

**Physical & Mechanical Properties**

22.86 **Clear Aperture CA (mm):**

**Diameter (mm):**

25.40 +0.00/-0.10

6.35 ±0.20 **Thickness (mm):**

<3 **Parallelism (arcmin):**

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

Fine Ground **Edges:**

0.16 **Poisson's Ratio:**

73 **Young's Modulus (GPa):**

522.00 **Knoop Hardness (kg/mm<sup>2</sup>):**

## Optical Properties

0 **Angle of Incidence (°):**

Laser Ultra V-Coat, IBS (1064nm) **Coating:**

1064 **Design Wavelength DWL (nm):**

Fused Silica (Corning 7980) **Substrate:**

1.458 **Index of Refraction (n<sub>d</sub>):**

10-5 **Surface Quality:**

67.8 **Abbe Number (v<sub>d</sub>):**

R<sub>abs</sub> <0.10% @ 1064nm **Coating Specification:**

M10 **Surface Flatness (P-V):**

15 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz **Damage Threshold, Certified:**

## Material Properties

2.20 **Density (g/cm<sup>3</sup>):**

0.52 (+5 to +35°C)  
0.57 (0 to +200°C)  
0.48 (-100 to +200°C) **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

7980 0F **Fused Silica Grade:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- IBS Coated for Minimal Absorption and Scatter
- <0.1% Reflectivity at Nd:YAG Laser Lines
- Certified Laser Damage Thresholds at Design Wavelength

TECHSPEC® IBS Laser Line Windows feature an ion beam sputtering (IBS) anti-reflection coating that provides <0.1% reflectivity at their design wavelength with minimal losses due to absorption or scatter. The IBS coating process produces dense, homogeneous coating layers that are environmentally stable and insensitive to temperature and humidity changes, enabling these windows to be used in harsh environments. TECHSPEC IBS Laser Line Windows are available in standard imperial sizes with designs for the Nd:YAG laser wavelengths of 355nm, 532nm, and 1064nm. In-house manufacturing enables Edmund Optics to provide custom sizes and designs in the wavelength range 343nm to 1600nm.

## Superpolished Optics for Minimized Scatter

LEARN  
MORE [▢](#)

### Compatible Mounts

---