

**TECHSPEC® 25.4mm Dia x 150mm FL, NIR I Imaging Grade PCX Cylinder Lens**



Stock #34-675 **10 In Stock**

⊖ 1 ⊕ €97.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €97,00 each                   |
| Qty 6-25       | €88,00 each                   |
| Qty 26-49      | €84,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

25.40 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

|  |                                     |
|--|-------------------------------------|
| 3.50                                   | Center Thickness CT (mm):           |
| ±0.1                                   | Center Thickness Tolerance (mm):    |
| 22.86                                  | Clear Aperture CA (mm):             |
| 2.45                                   | Edge Thickness ET (mm):             |
| <b>Optical Properties</b>              |                                     |
| 150.00                                 | Effective Focal Length EFL (mm):    |
| N-BK7                                  | Substrate: <input type="checkbox"/> |
| 6.00                                   | f#:                                 |
| 0.08                                   | Numerical Aperture NA:              |
| NIR I (600-1050nm)                     | Coating:                            |
| 600 - 1050                             | Wavelength Range (nm):              |
| 147.69                                 | Back Focal Length BFL (mm):         |
| R <sub>avg</sub> ≤ 0.5% @ 600 - 1050nm | Coating Specification:              |
| ±1                                     | Focal Length Tolerance (%):         |
| 77.52                                  | Radius R <sub>1</sub> (mm):         |
| 40-20                                  | Surface Quality:                    |
| 1.5λ                                   | Power (P-V) @ 632.8nm:              |
| λ/4                                    | Irregularity (P-V) @ 632.8nm:       |
| <5                                     | Plano Axis Wedge (arcmin):          |
| <5                                     | Power Axis Wedge (arcmin):          |

|                              |                             |
|------------------------------|-----------------------------|
| <b>Regulatory Compliance</b> |                             |
| Compliant                    | RoHS 2015:                  |
| View                         | Certificate of Conformance: |
| Compliant                    | Reach 235:                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

TECHSPEC® Imaging Grade PCX Cylinder Lenses offer an ideal pairing of tightly controlled tolerances and scalable pricing for volume integration. As opposed to spherical lenses, which focus light in two dimensions, cylinder lenses are used to focus light in one dimension. AR Coating options are available for laser applications, minimizing stray light and maximizing throughput of a system. Our TECHSPEC Imaging Grade PCX Cylinder Lenses are specified to control geometric characteristics in order to ensure consistent performance from design to manufacturing. Typical applications include circularizing elliptical beams from a laser diode, creating a light sheet for measurement systems, or projecting a laser line onto a surface.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC Imaging Grade PCV Cylinder Lenses](#).

**LASER OPTICS** MADE BY EDMUND OPTICS®



[LEARN MORE](#)