

[See all 293 Products in Family](#)

TECHSPEC<sup>®</sup> 25.4mm Dia. x 50.8mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-779-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€138<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €138,00 each                  |
| Qty 6-25       | €110,00 each                  |
| Qty 26-49      | €104,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| 25.40 ±0.025                         | Diameter (mm):                              |
| 24.40                                | Clear Aperture CA (mm):                     |
|                                      |                                             |
| <1                                   | Centering (arcmin):                         |
| 11.50 ±0.20                          | Center Thickness CT (mm):                   |
|                                      |                                             |
| 8.00 ±0.10                           | Center Thickness CT 1 (mm):                 |
| 3.50 ±0.10                           | Center Thickness CT 2 (mm):                 |
|                                      |                                             |
| 8.20                                 | Edge Thickness ET (mm):                     |
|                                      |                                             |
| Protective as needed                 | Bevel:                                      |
| Optical Properties                   |                                             |
| 50.80                                | Effective Focal Length EFL (mm):            |
| ±1                                   | Focal Length Tolerance (%):                 |
|                                      |                                             |
| 44.90                                | Back Focal Length BFL (mm):                 |
| 587.6                                | Focal Length Specification Wavelength (nm): |
|                                      |                                             |
| 33.54                                | Radius R <sub>1</sub> (mm):                 |
| -27.27                               | Radius R <sub>2</sub> (mm):                 |
|                                      |                                             |
| -101.50                              | Radius R <sub>3</sub> (mm):                 |
|                                      |                                             |
| N-SSK8 / SF56                        | Substrate: □                                |
|                                      |                                             |
| 40-20                                | Surface Quality:                            |
|                                      |                                             |
| 2.00                                 | f/#:                                        |
|                                      |                                             |
| 0.25                                 | Numerical Aperture NA:                      |
|                                      |                                             |
| VIS 0° (425-675nm)                   | Coating:                                    |
|                                      |                                             |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
|                                      |                                             |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
|                                      |                                             |
| 425 - 675                            | Wavelength Range (nm):                      |
|                                      |                                             |
| Regulatory Compliance                |                                             |
|                                      |                                             |
| View                                 | Certificate of Conformance:                 |
|                                      |                                             |

## Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- **MgF<sub>2</sub>** and **VIS-NIR** Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated Achromatic Lenses provide optimized transmission for 425 – 675nm, reducing average reflection to 0.4%. **MgF<sub>2</sub>** and **VIS-NIR** Coated Achromats are also available on our website.

## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts