

254mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-182 [CONTACT US](#)

⊖ 1 ⊕ €1.223,00

ADD TO CART

Qty 1-4	
€1.223,00	

Qty 5+
€1.101,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):	1064
Focal Length FL (mm):	254.00
Maximum Diameter (mm):	122
Scan Angle (°):	

±25.00
Scan Field (mm): 157.0 x 157.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Type: F-Theta Lens
Working Distance (mm): 304.6
Wavelength Range (nm): 1064
Flange Distance (mm): 360.6
Focus Size Diameter, 1/e² (µm): 25
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 76.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View