

TECHSPEC[®] 25.4mm Square x -50 FL, 355nm AR Coated, Laser Grade PCV Cylinder Lens



Stock #37-588 3 In Stock

-

1

+

€239^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€239,00 each
Qty 6-25	€216,00 each
Qty 26-49	€204,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cylinder Lens, Plano-Concave

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

3.00

Center Thickness CT (mm):

±0.1	Center Thickness Tolerance (mm):
22.86 x 22.86	Clear Aperture CA (mm):
+0.0/-0.025	Dimensional Tolerance (mm):
25.4 x 25.4	Dimensions (mm):
6.64	Edge Thickness ET (mm):
<3	Axial Twist (arcmin):

Optical Properties	
-50.00	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate:
2	f/#:
0.25	Numerical Aperture NA:
Laser V-Coat (355nm)	Coating:
-52.06	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 355nm	Coating Specification:
355	Design Wavelength DWL (nm):
587.6	Focal Length Specification Wavelength (nm):
22.93	Radius R ₁ (mm):
20-10	Surface Quality:
7.5 J/cm ² @ 355nm, 20ns, 20Hz	Damage Threshold, By Design:
1.5λ	Power (P-V) @ 632.8nm:
N4	Irregularity (P-V) @ 632.8nm:
<3	Plano Axis Wedge (arcmin):
<4.5	Power Axis Wedge (arcmin):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- <0.25% AR Coated for Nd:YAG Harmonics
- <3 Arcminute Wedge Tolerance
- Fused Silica Substrate

TECHSPEC® Laser Grade Laser Line Cylinder Lenses are manufactured with tightly controlled geometric wedge tolerances to facilitate drop in compatibility. These laser line cylinder lenses feature laser grade optical specifications including 20-10 surface quality and N4 surface irregularity on both plano and cylindrical surfaces. TECHSPEC Laser Grade Laser Line Cylinder Lenses are available in 266nm, 355nm, 532nm, and 1064nm AR coated versions, with

specified laser induced damage thresholds. These fused silica lenses are ideal for demanding laser machining and medical applications.

;