

TECHSPEC<sup>®</sup> 25mm Dia 0.11 NA, UV Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#21-932** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€599<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €599,00 each                  |
| Qty 6-10       | €539,00 each                  |
| Qty 11-25      | €503,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Aspheric Lens

Physical & Mechanical Properties

|                      |                           |
|----------------------|---------------------------|
| 25.00 +0/-0.025      | Diameter (mm):            |
| <1                   | Centering (arcmin):       |
| 22.5                 | Clear Aperture CA (mm):   |
| 3.85                 | Edge Thickness ET (mm):   |
| 5.50 ±0.1            | Center Thickness CT (mm): |
| Protective as needed | Bevel:                    |
| Plano                | Shape of Back Surface:    |

Optical Properties

|                                             |                                      |
|---------------------------------------------|--------------------------------------|
| 100.00 @ 355nm                              | Effective Focal Length EFL (mm):     |
| 0.11                                        | Numerical Aperture NA:               |
| 96.30 @ 355nm                               | Back Focal Length BFL (mm):          |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: <input type="checkbox"/>  |
| 355                                         | Aspheric Design Wavelength (nm):     |
| 0.4λ                                        | Asphere Figure Error, RMS @ 632.8nm: |
| UV (250-425nm)                              | Coating:                             |
| R <sub>avg</sub> ≤1.5% @ 250 - 425nm        | Coating Specification:               |
| 40-20                                       | Surface Quality:                     |
| 4                                           | f/#:                                 |
| 250 - 425                                   | Wavelength Range (nm):               |
| Infinite                                    | Conjugate Distance:                  |
| 10.00                                       | Power (diopters):                    |

Regulatory Compliance



|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 235:                  |

## Product Details

- Low Coefficient of Thermal Expansion
- Precision and High Precision Options
- High Numerical Apertures to Maximize Throughput

TECHSPEC® UV Fused Silica Aspheric Lenses offer the benefits of an aspheric element combined with the manufacturing precision of state-of-the-art grinding and polishing equipment. These fused silica optics can be easily designed and integrated into complex optical systems with the available prescription data. Featuring low *f*/#'s, which allow for a larger aperture and thus more light gathering and focusing performance, these fused silica lenses are computer-optimized to eliminate spherical and minimize higher order aberrations. TECHSPEC® UV Fused Silica Aspheric Lenses offer a low coefficient of thermal expansion, making them ideal for applications in metrology, beam-focusing or collimating, and OEM integration. These lenses are available in a variety of coating options and are offered in sizes ranging from 10-50mm.

## Technical Information



UV FS Transmission Curve

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts