

25.4mm Wire Grid Polarizing Cube



Stock **#89-604** **20+ In Stock**

- 1 + €530^{.00}

ADD TO CART

Volume Pricing

Qty 1-5	€530,00 each
Qty 6-24	€429,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

>90 **Clear Aperture (%):**

Wire Grid **Construction:**

25.4 x 25.4 x 25.4 ±0.3
Dimensions (mm):

Optical Properties

Beam Deviation (arcmin):
 <5

Coating Specification:
 R_{avg} <0.5% @ 400 - 700nm

Efficiency (T_p*R_s):
 >62% @ 450nm
 >65% @ 550nm & 650nm

Extinction Ratio:
 1000:1 @ 450nm
 2000:1 @ 550nm
 3000:1 @ 650nm

Substrate:
 N-BK7

Surface Quality:
 40-20

Transmission (%):
 T_p >72% @ 450nm
 T_p >75% @ 550nm
 T_p >78% @ 650nm

Transmitted Wavefront Distortion (RMS):
 <0.33λ @ 633nm

Wavelength Range (nm):
 400 - 700

Regulatory Compliance

RoHS 2015:
 Compliant

Certificate of Conformance:
 View

REACH 241:
 Compliant


Product Details

- High Contrast Over Large Angles of Incidence
- Low Color Shift at Large Angles
- Ideal for Uncollimated Light Sources


Wire Grid Polarizing Cube Beamsplitters are designed for applications using uncollimated light, such as with a broadband white light source. Wire Grid Polarizing Cube Beamsplitters consist of a wire grid polarizer cemented between two precision high tolerance right angle prisms. An anti-reflection coating has been applied to each face of the beamsplitter to provide less than 0.5% average reflection per surface. Additionally, these beamsplitters maintain their contrast spectrally from 400 – 700nm and over a large cone angle of ±25°.

Technical Information

Wire Grid Polarizing Cube Transmission of P-Polarization



Wire Grid Polarizing Cube Beamsplitter Contrast Ratio



Wavelength	Incident Cone of Light				
	±5°	±10°	±15°	±20°	±25°

400 - 500nm	2,100:1	2,000:1	1,600:1	1,400:1	1,100:1
500 - 600nm	4,000:1	3,900:1	2,900:1	2,600:1	1,900:1
600 - 700nm	6,000:1	5,500:1	4,200:1	3,800:1	2,500:1

;