

**TECHSPEC®** 25.4mm x -100mm FL, NIR II Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-644** 3-4 DAYS

⊖ 1 ⊕ **€111,00**

ADD TO CART

Qty 1-5

€111,00

Qty 6+

€88,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.40 +0.0/-0.025

**Effective Focal Length EFL (mm):**  
-100.00

**Substrate:** □  
[N-BK7](#)

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>f/#:</b><br>4                                                                                                                                        |
| <b>Numerical Aperture NA:</b><br>0.13                                                                                                                   |
| <b>Coating:</b><br>NIR II (750-1550nm)                                                                                                                  |
| <b>Type:</b><br>Cylinder Lens, Plano-Concave                                                                                                            |
| <b>Wavelength Range (nm):</b><br>750 - 1550                                                                                                             |
| <b>Back Focal Length BFL (mm):</b><br>-102.31                                                                                                           |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                             |
| <b>Center Thickness CT (mm):</b><br>3.50                                                                                                                |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1                                                                                                         |
| <b>Clear Aperture CA (mm):</b><br>22.86                                                                                                                 |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| <b>Edge Thickness ET (mm):</b><br>5.03                                                                                                                  |
| <b>Radius R<sub>1</sub> (mm):</b><br>51.68                                                                                                              |
| <b>Surface Quality:</b><br>40-20                                                                                                                        |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                                   |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                             |
| <b>Plano Axis Wedge (arcmin):</b><br><5                                                                                                                 |
| <b>Power Axis Wedge (arcmin):</b><br><5                                                                                                                 |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |