

TECHSPEC® 25mm 50R/50T Cube Beamsplitter



Stock #32-505 [CONTACT US](#)

⊖ 1 ⊕ €278.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €278,00 each |
| Qty 6-25 | €222,00 each |
| Qty 26-99 | €204,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

Cube **Construction:**

25.0 x 25.0 x 25.0 ±0.10
Dimensions (mm):

Optical Properties

±3
Beam Deviation (arcmin):

N4 MgF₂ @ 550nm on Faces
Multilayer Dielectric on Hypotenuse
Coating:

50/50
Reflection/Transmission Ratio (RT):

±5
Reflection/Transmission Tolerance (%):

N-BK7
Substrate:

60-40
Surface Quality:

400 - 700
Wavelength Range (nm):

1.25
Power (fringes) @ 632.8nm:

0.25
Irregularity (fringes) @ 632.8nm:

Regulatory Compliance

Compliant
RoHS 2015:

View
Certificate of Conformance:

Compliant
Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

Output is partially polarized. If polarization sensitivity is critical to your application, we recommend using [TECHSPEC® Polarizing Beamsplitters](#) or [TECHSPEC® Non-Polarizing Beamsplitters](#).

- Multi-Layer Dielectric Coating
- Available in 30/70, 70/30, or 50/50 Split Ratios
- Optimal for Applications Insensitive to Polarization

TECHSPEC® Cube Beamsplitters are constructed by cementing two right angle prisms together and are offered in a range of reflection/transmission ratios. Output is partially polarized, making this product suitable for illumination and other applications where polarization is not a concern. TECHSPEC® Cube Beamsplitters feature an interference coating which is applied to the hypotenuse surface of one of the prisms to provide the designated reflection/transmission ratio with minimal absorption loss.

Note: If polarization sensitivity is critical to your application, we recommend using [TECHSPEC® Polarizing Beamsplitters](#) or [TECHSPEC® Non-Polarizing Beamsplitters](#).

Technical Information



