

**TECHSPEC® 25mm Dia. x 30mm FL, VIS Coated, Hybrid Asphere**



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock **#66-003** CLEARANCE 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€99,00**

ADD TO CART

Qty 1-24

€99,00

Qty 25+

€79,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
25.00 +0.00/-0.10

**Effective Focal Length EFL (mm):**  
30.00 @ 587.6nm

**Numerical Aperture NA:**  
0.42

|                                                                                                                    |
|--------------------------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>25.82                                                                        |
| <b>Substrate:</b> <br>Zeonex E48R |
| <b>Aspheric Design Wavelength (nm):</b><br>587.6                                                                   |
| <b>Coating:</b><br>BBAR (425-675nm)                                                                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.75% @425 - 675nm                                              |
| <b>Surface Quality:</b><br>60-40                                                                                   |
| <b>Clear Aperture CA (mm):</b><br>23.00                                                                            |
| <b>Edge Thickness ET (mm):</b><br>3.6                                                                              |
| <b>Center Thickness CT (mm):</b><br>7.30 ±0.10                                                                     |
| <b>f/#:</b><br>1.2                                                                                                 |
| <b>Bevel:</b><br>Protective bevel as needed                                                                        |
| <b>Operating Temperature (°C):</b><br>-30 to +70                                                                   |
| <b>Radius R<sub>2</sub> (mm):</b><br>120                                                                           |
| <b>Shape of Back Surface:</b><br>Convex                                                                            |
| <b>Type:</b><br>Aspheric Lens                                                                                      |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                                         |
| <b>Conjugate Distance:</b><br>Infinite                                                                             |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |