

TECHSPEC®

25mm Dia. Linear Polarizing Film (XP42-75)



Stock **#19-016** CLEARANCE 3-4 DAYS

-

1

+

€9,95

ADD TO CART

Qty 1+

€9,95

Volume Pricing

[Request Quote](#)

i Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate: [Polymer Film XP42-75](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm):
0.77 ±0.08

Transmission (%) : Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)
Type : Linear Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film
Note : Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.98 (nominal at 555nm)
Transmission Variance after 1000 Hours (%) : <±5
#Sorting : 27.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant