


TECHSPEC® 25mm Dia., Ultrafast-Enhanced Silver, Metallic Coated Stemmed Mirror



TECHSPEC® Stemmed Mirrors



Stock **#17-553** CLEARANCE 3-4 DAYS

⊖ 1 ⊕

€174,00

ADD TO CART

Qty 1-5

€174,00

Qty 6+

€139,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
22.50

Coating:

Ultrafast-Enhanced Silver (600-1000nm)
Diameter (mm): 25.00 +0.00/-0.10
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Clear Aperture (%) : 90.00
Back Surface: Commercial Polish
Coating Specification: R _{avg} >99% @ 600 - 1000nm (0°, All Polarizations) R _{avg} >99% @ 540 - 1000nm (45°, S-Polarization) R _{avg} >98.5% @ 730 - 870nm (45°, P-Polarization)
Wavelength Range (nm): 600 - 1000
Surface Flatness (P-V): λ/10
Coating Type: Ultrafast-Enhanced Silver
Damage Threshold, Reference: ☐ 0.3 J/cm ² @ 48fs FWHM, 100Hz @ 800nm (S-Polarization) 0.16 J/cm ² @ 48fs FWHM, 100Hz @ 800nm (S-Polarization)
GDD Specification: 0 ±20fs ² @ 600 - 1050nm
Stem Diameter (mm): 12.50 +0.00/-0.10
Compatible Kinematic Mount: #58-853
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View