

[See all 447 Products in Family](#)

TECHSPEC<sup>®</sup> 25mm Dia., 4mm Thick, YAG-BBAR Coated,  $\lambda$ /4 N-BK7 Window



Stock #13-319 12 In Stock

-

1

+

€114<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €114,00 each                  |
| Qty 6-25       | €91,00 each                   |
| Qty 26-49      | €85,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

90

Clear Aperture (%):

|                  |                          |
|------------------|--------------------------|
| 22.50            | Clear Aperture CA (mm):  |
| 25.00 +0.0/-0.25 | Diameter (mm):           |
| 4.00 ±0.20       | Thickness (mm):          |
| Fine Ground      | Edges:                   |
| 610.00           | Knoop Hardness (kg/mm²): |
| <1               | Parallelism (arcmin):    |
| 0.21             | Poisson's Ratio:         |
| 82               | Young's Modulus (GPa):   |

| Optical Properties                                                                                           |                                        |
|--------------------------------------------------------------------------------------------------------------|----------------------------------------|
| 64.17                                                                                                        | Abbe Number (v <sub>d</sub> ):         |
| YAG-BBAR (500-1100nm)                                                                                        | Coating:                               |
| R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm | Coating Specification:                 |
| 1.516                                                                                                        | Index of Refraction (n <sub>d</sub> ): |
| N-BK7                                                                                                        | Substrate:                             |
| λ/4                                                                                                          | Surface Flatness (P-V):                |
| 60-40                                                                                                        | Surface Quality:                       |
| 500 - 1100                                                                                                   | Wavelength Range (nm):                 |
| 5 J/cm² @ 532nm, 10ns                                                                                        | Damage Threshold, By Design: □         |

| Material Properties                       |                                                              |
|-------------------------------------------|--------------------------------------------------------------|
| 7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 2.51                                      | Density (g/cm³):                                             |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details


- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

TECHSPEC® λ/4 N-BK7 Precision Windows are ideally suited for industrial and low-power laser applications. The high tolerance design yields minimal beam distortion and scatter. Broadband coating options extend the range of these precision windows through the visible and near-infrared spectra. TECHSPEC® λ/4 N-BK7 Precision Windows are offered in circular and rectangular sizes ranging from 2mm to 200mm.

**Note:** New additions to this product family may be specified with a transmitted wavefront distortion (TWD) specification instead of a surface flatness. For more information on the difference between these two specifications, see our application note on [Understanding Optical Windows](#).

## Technical Information


| N-BK7                               |  |
|-------------------------------------|--|
| Uncoated N-BK7 Typical Transmission |  |



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

**N-BK7 with MgF<sub>2</sub> Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with VIS-EXT Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with VIS-NIR Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with VIS 0° Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

