

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia. X 125mm FL, VIS 0⁺ Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock #48-987 3-4 DAYS

[Other Coating Options](#)



1



€142,00

ADD TO CART

Qty 1-5

€142,00

Qty 6+

€113,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Back Focal Length BFL (mm): 123.82
Effective Focal Length EFL (mm): 125.00
Coating: VIS 0° (425-675nm)
Coating Specification: Ravg ≤0.4% @ 425 - 675nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.42 ±0.10
Edge Thickness ET (mm): 2.05
Radius R ₁ =R ₂ (mm): 114.08
Clear Aperture CA (mm): 24.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant