

25mm Dia., Extended Hot Mirror



Extended Hot Mirrors

Stock #46-386 **20+ In Stock**

⊖ 1 ⊕ €74.⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | €74,00 each |
| Qty 10-25 | €66,50 each |
| Qty 26-49 | €63,50 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Shortpass Filter **Type:**

Physical & Mechanical Properties

25.00 ±0.25 **Diameter (mm):**

Thickness (mm):

3.30 ±0.2

≥85 **Clear Aperture (%)**

Ground **Edges:**

Optical Properties

Dielectric **Coating Type:**

Hot Mirror, 0° **Coating:**

4 - 6λ **Surface Flatness (P-V):**

425 - 1600 **Wavelength Range (nm):**

BOROFLOAT® **Substrate:** □

0.00 **Angle of Incidence (°):**

Coating Specification:
R_{avg} ≥90% @ 750 - 1150nm
R_{avg} ≥80% @ 1200 - 1600nm
T_{avg} ≥85% @ 425 - 675nm

80-50 **Surface Quality:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**



Product Details

- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts
