

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia. X 200mm FL, NIR II Coated, Achromatic Lens



Stock #47-271 3-4 DAYS

[Other Coating Options](#)



1



€133,00

ADD TO CART

Qty 1-5

€133,00

Qty 6+

€106,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

200.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 193.761
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 6.00 ±0.10
Center Thickness CT 2 (mm) : 4.00 ±0.10
Radius R₁ (mm) : 112.88
Radius R₂ (mm) : -112.88
Radius R₃ (mm) : -1415.62
Edge Thickness ET (mm) : 9.25
Substrate:  N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 8.00
Numerical Aperture NA : 0.06
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View