

TECHSPEC<sup>®</sup> 25mm Dia x -100mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-669** 4 In Stock

-

1

+

€59<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €59,00 each                   |
| Qty 6-25       | €47,00 each                   |
| Qty 26-49      | €45,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

25.00

Diameter (mm):

Center Thickness CT (mm):

|           |                             |
|-----------|-----------------------------|
| 3.00      |                             |
| 90.00     | Clear Aperture (%):         |
| +0.0/-0.1 | Dimensional Tolerance (mm): |
| 2.61      | Edge Thickness ET (mm):     |
| 200.0     | Radius R (mm):              |
| ±0.1      | Thickness Tolerance (mm):   |

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Optical Properties                 |                                     |
| -100.00                            | Focal Length FL (mm):               |
| Enhanced Aluminum (450-650nm)      | Coating:                            |
| R <sub>avg</sub> >95% @450 - 650nm | Coating Specification:              |
| Metal                              | Coating Type:                       |
| ±2                                 | Focal Length Tolerance (%):         |
| N-BK7                              | Substrate: <input type="checkbox"/> |
| λ/2                                | Surface Accuracy:                   |
| 60-40                              | Surface Quality:                    |
| 450 - 650                          | Wavelength Range (nm):              |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 247:                  |

## Product Details

- Precision Polished Surface
  - λ/2 Surface Accuracy
  - Variety of Coating Options Offered
- TECHSPEC® Convex Mirrors are ideal for expanding an imaging system's field of view without introducing chromatic aberrations. TECHSPEC Convex Mirrors utilize a precision polished surface with a λ/2 surface accuracy to maintain image quality. These optical mirrors create virtual, upright images. Shorter focal lengths generate wider fields of view, while longer focal lengths minimize distortion.

## Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).