


## TECHSPEC® 25mm Dia. x -50mm FL, Uncoated, Double-Concave Lens



Stock #32-996 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€32,50**

ADD TO CART

Qty 1-9

€32,50

Qty 10+

€29,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

-50.00

Substrate:

[N-BK7](#)

f#:  
2.00

Numerical Aperture NA:  
0.25

Coating:  
Uncoated

Type:  
Double-Concave Lens

Wavelength Range (nm):  
350 - 2200

Back Focal Length BFL (mm):  
-50.82

Bevel:  
Protective bevel as needed

Center Thickness CT (mm):  
2.50

Center Thickness Tolerance (mm):  
±0.10

Centering (arcmin):  
<1

Clear Aperture CA (mm):  
24.00

Edge Thickness ET (mm):  
5.40

Focal Length Specification Wavelength (nm):  
587.6

Focal Length Tolerance (%):  
±1

Radius  $R_1=-R_2$  (mm):  
-52.10

Surface Quality:  
40-20

Power (P-V) @ 632.8nm:  
1.5λ

Irregularity (P-V) @ 632.8nm:  
λ/4

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Reach 219:  
[Compliant](#)

Certificate of Conformance:  
[View](#)