

[See all 4 Products in Family](#)

25mm Diameter High Contrast Mid-Wave Infrared Polarizer



Stock #90-387 NEW **1 In Stock**

€1.855⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	€1.855,00 each
Qty 11+	€1.485,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer Type:

Physical & Mechanical Properties

23.75 Clear Aperture CA (mm):

25.00 +0.0/-0.2 Diameter (mm):

2.00 ±0.50	Thickness (mm):
Nanoparticle	Construction:
95	Clear Aperture (%):
Optical Properties	
Uncoated	Coating:
>10,000:1 (2000-4500nm) >1,000:1 (1500-5000nm)	Extinction Ratio:
Sodium Silicate Glass Doped with Glass Nanoparticles	Substrate: □
60-40	Surface Quality:
>65 (2000nm-4500nm) >35 (1500-5000nm)	Transmission (%):
<3 waves @ 633nm per 1cm	Transmitted Wavefront, P-V:
<20	Beam Deviation (arcmin):
<0.5 (to indicated edge)	Polarization Axis Mark (%):
1500 - 5000	Wavelength Range (nm):
±20	Acceptance Angle (°):

Threading & Mounting

Unmounted	Mount Thickness (mm):
-----------	------------------------------

Environmental & Durability Factors

-50 to +400	Operating Temperature (°C):
-------------	------------------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- 1.5 – 5µm Wavelength Range
- Mounted for Easy Handling and System Integration
- Highly Durable Soda Lime Substrate

Featuring high contrast ratios and transmittances, Mid-Wave Infrared (MMIR) Polarizers are designed for applications operating in the 1.5 – 5µm wavelength range. Ideal for harsh environments, each MMR polarizer is constructed of a dichroic glass substrate which provides a high resistance to UV radiation and chemicals, as well as an operating temperature of up to 400°C.