

25mm Diameter Mid-Wave Infrared Polarizer



Stock **#85-264** [CONTACT US](#)

-

1

+

€2.065^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€2.065,00 each
Qty 6+	€1.660,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Linear Polarizer	Type:
Physical & Mechanical Properties	
20.8	Clear Aperture CA (mm):
25.00	Diameter (mm):

5.00	Thickness (mm):
Nanoparticle	Construction:
Optical Properties	
±20	Angle of Incidence (°):
>1,000:1 (1500-5000nm) >10,000:1 (2000-4500nm)	Extinction Ratio:
Soda Lime Float Glass	Substrate:
60-40	Surface Quality:
35 (1500-5000nm) 65 (2000-4500nm)	Transmission (%):
<3λ per 10mm	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
±2	Polarization Axis Mark (%):
1500 - 5000	Wavelength Range (nm):
1 W/cm² (Continuous Block) 5 W/cm² (Continuous Pass)	Damage Threshold, By Design:

Environmental & Durability Factors	
-20 to +120	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- 1.5 – 5μm Wavelength Range
- Mounted for Easy Handling and System Integration
- Highly Durable Soda Lime Substrate

Featuring high contrast ratios and transmittances, Mid-Wave Infrared (MMIR) Polarizers are designed for applications operating in the 1.5 – 5μm wavelength range. Ideal for harsh environments, each MMIR polarizer is constructed of a dichroic glass substrate which provides a high resistance to UV radiation and chemicals, as well as an operating temperature of up to 400°C.