

TECHSPEC[®] 25mm FL f/5.6, Blue Series M12 Lens



25mm FL Blue Series M12 Lens



Stock #83-944 20+ In Stock

-

1

+

€81^{.00}

ADD TO CART

Volume Pricing	
Qty 1-49	€81,00 each
Qty 50+	€64,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Blue Series

Series:

M12 Imaging Lens

Type:

IR Cut Filter:

No	
	Imaging Lens Type:
High Performance M12 Lens	
Physical & Mechanical Properties	
	Iris Option:
Fixed	
	Length (mm):
30.00	
	Maximum Diameter (mm):
18	
	Outer Diameter (mm):
18	
	Weight (g):
12	
Optical Properties	
	Horizontal Field of View @ Max Sensor Format:
16.2°	
	Field of View at Max Sensor Format:
Horizontal: 40.0mm - 16.2° Vertical: 26.5mm - 10.9° Diagonal: 44.3mm - 18°	
	Horizontal Field of View, 1/1.8" Sensor:
40.0mm - 16.2°	
	Horizontal Field of View, 1/2" Sensor:
35.4mm - 14.5°	
	Horizontal Field of View, 1/2.5" Sensor:
32.1mm - 13.1°	
	Horizontal Field of View, 1/3" Sensor:
26.5mm - 10.9°	
	Horizontal Field of View, 1/4" Sensor:
19.9mm - 8.2°	
	Maximum Image Circle (mm):
9.00	
	Numerical Aperture NA, Object Side:
0.0146	
	Number of Elements (Groups):
6(5)	
	Wavelength Range (nm):
400 - 700	
	Focal Length FL (mm):
25.00	
	Working Distance (mm):
150 - ∞	
	Aperture (f/#):
f/5.6	
	Distortion (%):
0.59 @ Full Field	
	Back Focal Length BFL (mm):
8.5 - 6.5	
	Coating Specification:
M4 MgF ₂ @ 550nm	
	Entrance Pupil Position (mm):
4.15	
	Object Space Principal Plane (mm):
11.90	
	Image Space Principal Plane (mm):
-19.03	
	Maximum Distortion (%):
-0.59	
	Exit Pupil Position (mm):
-30.25	
	Lens Wavelength Range:
VIS	
Sensor	
	Maximum Sensor Format:
1/1.8"	
	Pixel Size (µm):
1.40	
Threading & Mounting	
	Filter Thread:
N/A	

S-Mount (M12 x0.5)	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- Ruggedized Designs** Also Available


TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our **TECHSPEC® Green Series M12 Lenses**. Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras (**#53-675**) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring (**#59-241**) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a **Request for Prescription Form**.

Note: Compatible **TECHSPEC® M12 Imaging Lens Accessories** available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses: High resolution finite conjugate designs optimized for machine vision working distances.
- Rugged Blue Series M12 Lenses:** **Stabilized ruggedization** versions of our Blue Series M12 Lenses, utilizing the same optics.
- Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Distortion Plot



#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Relative Illumination Plot




#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Working Distance versus Field of View Plot



#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f5.6



#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Depth of Field Plot, 150mm Working Distance, f5.6




#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f5.6



#83-944, 25mm FL f/5.6, Blue Series M12 Lens, Depth of Field Plot, 400mm Working Distance, f5.6

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm

12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm



*Specified for Optimized Working Distance of 150 - 250mm.