

TECHSPEC® 25mm H x 50mm L x -40mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-063 3-4 DAYS

⊖ 1 ⊕ **€108,00**

ADD TO CART

Qty 1-5

€108,00

Qty 6+

€86,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):

-40.00

Substrate:

[N-SF11](#)

Coating:

Uncoated

Type:
Cylinder Lens, Plano-Concave

Wavelength Range (nm):
400 - 2500

Back Focal Length BFL (mm):
-42.24

Center Thickness CT (mm):
4.00

Center Thickness Tolerance (mm):
±0.1

Dimensional Tolerance (mm):
+0.0/-0.2

Dimensions (mm):
25.0 x 50.0

Edge Thickness ET (mm):
6.47

Focal Length Tolerance (%):
±3

Radius R₁ (mm):
-31.39

Surface Quality:
60-40

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)